



Bi-hexagon socket, 3/8 inch, Width across flats: 11 mm



Order data

Order number	637000 11
GTIN	4018754001941
Item class	63A

Description

Version:

Forged from high quality steel, internally bevelled for easy fitting to bolt heads. Internal square to **DIN 3120**.

Optimum grain orientation due to special forging process. Close tolerance sockets with **AS drive** profile protect corners of bolt head. Hardened in an oil bath, stress-relieved and distortion-free for a precision fit. Smoothed finish.

Standard:

DIN 3124

Material:

HPQ® high performance steel, non-flaking chrome-plated over nickel.

Note:

PLEASE NOTE!

An alternative from GARANT is also available for this product.

Recommended product number: 637029

Technical description

Length	27 mm
Width across flats	11 mm
Ø drive output end	15.6 mm
Square drive	3/8 in

Drive profile	Bi-hex socket
Type of product	Socket insert