



## Double open ended spanner DIN 895, Widths across flats: 19X24mm



### Order data

Order number	613000 19X24
GTIN	4045197384584
Item class	62A

### Description

**Version:**

Drop forged, jaw angle 15°, strong shaft.

**Standard:**

**DIN 895**

**Material:**

Special steel (strength 1200 – 1400 N/mm<sup>2</sup>).

Black oxidised finish.

### Technical description

Width across flats 2	24 mm
maximum jaw height h	9.5 mm
Width across flats 1	19 mm
Width across flats	metric
Spanner length L	220 mm
Standard	DIN 895
Jaw position 1	15 degrees
Jaw position 2	15 degrees
Material	Special steel
Surface	burnished
Type of product	Spanner

