

**Double open ended spanner DIN 895, Widths across flats: 46X50mm****Order data**

Order number	613000 46X50
GTIN	4045197384690
Item class	62A

**Description****Version:**

Drop forged, jaw angle 15°, strong shaft.

**Standard:**

**DIN 895**

**Material:**

Special steel (strength 1200 – 1400 N/mm<sup>2</sup>).  
Black oxidised finish.

**Technical description**

maximum jaw height h	17 mm
Width across flats 1	46 mm
Width across flats 2	50 mm
Width across flats	metric
Spanner length L	440 mm
Standard	DIN 895
Jaw position 1	15 degrees
Jaw position 2	15 degrees
Material	Special steel
Surface	burnished
Type of product	Spanner

