

**Double open ended spanner DIN 895, Widths across flats: 24X27mm****Order data**

Order number	613000 24X27
GTIN	4045197384607
Item class	62A

**Description****Version:**

Drop forged, jaw angle 15°, strong shaft.

**Standard:**

**DIN 895**

**Material:**

Special steel (strength 1200 – 1400 N/mm<sup>2</sup>).

Black oxidised finish.

**Technical description**

maximum jaw height h	10.5 mm
Width across flats 2	27 mm
Width across flats 1	24 mm
Width across flats	metric
Spanner length L	255 mm
Standard	DIN 895
Jaw position 1	15 degrees
Jaw position 2	15 degrees
Material	Special steel
Surface	burnished
Type of product	Spanner

