



Hexagon socket, 3/8 inch, Width across flats: 19mm



Order data

Order number	637200 19
GTIN	4018754003006
Item class	63A

Description

Version:

Forged from high quality steel, internally bevelled for easy fitting to bolt heads. Internal square to **DIN 3120**.

Optimum grain orientation due to special forging process. Close tolerance sockets with **AS drive** profile protect corners of bolt head. Hardened in an oil bath, stress-relieved and distortion-free for a precision fit. Smoothed finish.

Standard:

DIN 3124

Material:

HPQ® high performance steel, non-flaking chrome-plated over nickel.

Note:

PLEASE NOTE!

An alternative from GARANT is also available for this product.

Recommended product number: 637229

Technical description

Width across flats	19 mm
Ø drive output end	25.2 mm
Length	32 mm
Square drive	3/8 in

Standard	DIN 3124
Drive profile	Hexagon socket
Material	HPQ® high performance steel
Surface	chromium-plated over nickel
with AS Drive profile.	yes
Type of product	Socket insert