

**Double open ended spanner DIN 895, Widths across flats: 24X30mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 613000 24X30  |
| GTIN         | 4045197384614 |
| Item class   | 62A           |

**Description****Version:**

Drop forged, jaw angle 15°, strong shaft.

**Standard:**

**DIN 895**

**Material:**

Special steel (strength 1200 – 1400 N/mm<sup>2</sup>).

Black oxidised finish.

**Technical description**

|                      |               |
|----------------------|---------------|
| maximum jaw height h | 11.5 mm       |
| Width across flats 1 | 24 mm         |
| Width across flats 2 | 30 mm         |
| Width across flats   | metric        |
| Spanner length L     | 285 mm        |
| Standard             | DIN 895       |
| Jaw position 1       | 15 degrees    |
| Jaw position 2       | 15 degrees    |
| Material             | Special steel |
| Surface              | burnished     |
| Type of product      | Spanner       |

