



## Bi-hexagon socket, 3/8 inch, Width across flats: 16mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 637000 16     |
| GTIN         | 4018754001996 |
| Item class   | 63A           |

### Description

#### Version:

Forged from high quality steel, internally bevelled for easy fitting to bolt heads. Internal square to **DIN 3120**.

Optimum grain orientation due to special forging process. Close tolerance sockets with **AS drive** profile protect corners of bolt head. Hardened in an oil bath, stress-relieved and distortion-free for a precision fit. Smoothed finish.

#### Standard:

**DIN 3124**

#### Material:

HPQ® high performance steel, non-flaking chrome-plated over nickel.

#### Note:

**PLEASE NOTE!**

An alternative from GARANT is also available for this product.

Recommended product number: 637029

### Technical description

|                    |         |
|--------------------|---------|
| Width across flats | 16 mm   |
| Ø drive output end | 21.7 mm |
| Length             | 31 mm   |
| Square drive       | 3/8 in  |

|                 |               |
|-----------------|---------------|
| Drive profile   | Bi-hex socket |
| Type of product | Socket insert |