



## Hexagon socket, 3/8 inch, Width across flats: 11 mm



### Order data

Order number	637200 11
GTIN	4018754002924
Item class	63A

### Description

#### Version:

Forged from high quality steel, internally bevelled for easy fitting to bolt heads. Internal square to **DIN 3120**.

Optimum grain orientation due to special forging process. Close tolerance sockets with **AS drive** profile protect corners of bolt head. Hardened in an oil bath, stress-relieved and distortion-free for a precision fit. Smoothed finish.

#### Standard:

**DIN 3124**

#### Material:

HPQ® high performance steel, non-flaking chrome-plated over nickel.

#### Note:

**PLEASE NOTE!**

An alternative from GARANT is also available for this product.

Recommended product number: 637229

### Technical description

Width across flats	11 mm
Ø drive output end	15.6 mm
Length	27 mm
Square drive	3/8 in

Standard	DIN 3124
Drive profile	Hexagon socket
Material	HPQ® high performance steel
Surface	chromium-plated over nickel
with AS Drive profile.	yes
Type of product	Socket insert