



## Diamond grinding disc PREMIUM\*\*\* for stone, Disc Ø: 100mm



### Order data

Order number	569640 100
GTIN	9003173565698
Item class	53T

### Description

#### Version:

Robust thin steel disc with brazed diamond segments, which are bedded in a special material. High **removal rate**, **extremely long working life** with **low vibration** (clean surfaces), for dry grinding.

#### Application:

For grinding, correcting, smoothing of stone and concrete using angle grinders. Optimum speed 10,000 – 12,000 rpm. Maximum speed 15,000 rpm.

#### Material:

Suitable for concrete.

### Technical description

Carrier body	Steel disc
Bore Ø	22.23 mm
Shape description	flat
Disc Ø	100 mm

Grinding media	Diamond
Grinding medium code	D
optimised for material	Stone
Propulsive equipment	Angle grinders
recommended speed	10000 - 12000 min <sup>-1</sup>
maximum speed	15000 min <sup>-1</sup>
Type of product	Sanding pad