

HOLEX

Abrasice flap brush, non-woven sinusoidal, Ø 100 × 100 mm, Grit equivalent: 180



Order data

Order number	568480 180
GTIN	4045197526779
Item class	52E

Description

Version:

Standard size Ø 100×100 mm or narrow version Ø 100×50 mm for grinding smaller areas. Mounting bore Ø 19 mm with multiple splines.

Sinusoidal abrasive fleece without cut edges. Impregnated with Aluminium Oxide (A).

Application:

For **matting** and **polishing** without abrupt changes in texture.

Note:

For matching the width of narrow rollers Ø 100×50 mm use the spacer ring pack No. 568439.

Technical description

Grinding media backing	Cleaning non-woven abrasive mesh
recommended speed	2800 min ⁻¹
Grit equivalent	180
Iron, sulphur and chlorine constituents	< 0.1 %
Roller Ø	100 mm

Roller width	100 mm
Product name attribute	Ø 100 × 100 mm
Type of product	Abrasive flap wheel roller, fleece

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Paint	suitable only under restricted conditions		
dry	suitable		