



## Abrasive flap wheel roller, fleece (A), Ø 100 × 50 mm, Grit equivalent: 280



### Order data

Order number	568474 280
GTIN	4045197680648
Item class	52E

### Description

#### Version:

Standard size Ø 100×100 mm or narrow version Ø 100×50 mm for grinding smaller areas.  
Mounting bore Ø 19 mm with multiple splines.  
Fleece impregnated with Aluminium Oxide (A).

#### Application:

Fine fleece **for light cleaning work** and **a uniform surface finish.**

#### Note:

For matching the width of narrow rollers Ø 100×50 mm use the spacer ring pack No. 568439.

### Technical description

recommended speed	2800 min <sup>-1</sup>
Grinding media backing	Cleaning non-woven abrasive mesh
Grit equivalent	280
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %

Roller Ø	100 mm
Roller width	50 mm
Product name attribute	Ø 100 × 50 mm
Bore Ø	19 mm
Type of product	Abrasive flap wheel roller, fleece

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Paint	suitable only under restricted conditions		
dry	suitable		