

**3M****Mini-linishing belt Ø 90×100 mm, SC-BF, Grit equivalent: 280****Order data**

Order number	568561 280
GTIN	4001895524592
Item class	53M

**Description****Version:**

Mini linishing belts Ø **90×100 mm** (289×100 mm).

Fleece mini-linishing belts for blending in, matting and finishing.

With film backing, for light-duty use on all backing rollers.

**Application:**

For use on surface grinding and burnishing machines with backing rollers No. 568570 – 568577 (mounting bore Ø 19 mm). Maximum speed 5000 rpm.

**Technical description**

Grit equivalent	280
Linishing belt Ø	90 mm
Colour	blue
Linishing belt width	100 mm
Linishing belt length	289 mm
Version	A very fine
Iron, sulphur and chlorine constituents	< 0.1 %

Manufacturer's designation	SC-BF
Type of product	Finishing belt

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable only under restricted conditions		
Wood	suitable		
Paint	suitable		
Uni	suitable		
dry	suitable		

## Accessories

Backing roller Ø 90×100 mm Type AIR	568575 AIR
-------------------------------------	------------