



Flange mounted transducer "FMT", maximum torque: 1500N·m



Order data

Order number	654350 1500
GTIN	5060922233110
Item class	66D

Description

Version:

- **Static sensors complete with cable (2 m) for direct connection to No. 654300 or No. 654340 (automatic detection of calibration data).**
- **Direct fixing to the workbench with 3 screws (not included).**

Supplied with:

UKAS calibration certificate on the right.

Up to and including size 150 with screw tightening simulator for checking electric and pneumatic screwdrivers. In a sturdy plastic case.

Note:

Not suitable for impact wrenches.

Technical description

Square socket	3/4 in
Square socket	1 in
maximum torque	1500 Nm
Measuring range	30 - 1500 Nm
Direction of tightening	Right-hand tightening
Torque measuring accuracy	± 0.5 %

Test certificate	Manufacturer's test certificate
Type of product	Torque testing device