



## Abrasive flap wheel roller, fabric, slit (A), Ø 100 × 100 mm, Grit: 60



### Order data

Order number	568466 60
GTIN	4045197526694
Item class	52E

### Description

#### Version:

**Flap strips of abrasive cloth** around the shank of the flap brush. Standard size **Ø 100×100 mm** or narrow version **Ø 100×50 mm** for grinding smaller areas. Mounting bore Ø 19 mm with multiple splines.

Abrasive cloth slit.

#### Application:

For **gentle longitudinal strokes** even on slightly convex surfaces, particularly versatile.

#### Note:

For matching the width of narrow rollers Ø 100×50 mm use the spacer ring pack No. 568439.

### Technical description

Grit	60
recommended speed	3700 min <sup>-1</sup>
Grinding media backing	Fabric
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
Roller Ø	100 mm

Roller width	100 mm
Product name attribute	Ø 100 × 100 mm
Type of product	Flap wheel roller fabric, slit

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable only under restricted conditions		
dry	suitable		