

**3M**
**Mini-linishing belt Ø 90×100 mm, 237AA, Grit: 280**

**Order data**

Order number	568550 280
GTIN	4001895606465
Item class	53M

**Description**
**Version:**

Mini-belts Ø 90×100 mm (289×100 mm).

The fine-structured pyramidal surface guarantees the **best finish and very long working life**. Particularly suitable for the intermediate grinding of stainless steel sheets.

**Application:**

For use on surface grinding and burnishing machines with backing rollers No. 568570 / 568575 (mounting bore Ø 19 mm). Maximum speed 5000 rpm.

Grinding medium code: A

Iron, sulphur and chlorine constituents: < 0.1 %

3M grit designation: A065

**Technical description**

3M grit designation	A065
Grit	280
Linishing belt width	100 mm
Linishing belt Ø	90 mm
Grinding medium code	A

Iron, sulphur and chlorine constituents	< 0.1 %
Manufacturer's designation	237AA

---

## Accessories

Backing roller Ø 90×100 mm Type SOFT	568580 SOFT
--------------------------------------	-------------