



Abrasive flap wheel roller, fleece (A), Ø 100 × 100 mm, Grit equivalent: 180



Order data

Order number	568475 180
GTIN	4045197526748
Item class	52E

Description

Version:

Standard size Ø 100×100 mm or narrow version Ø 100×50 mm for grinding smaller areas.

Mounting bore Ø 19 mm with multiple splines.

Fleece impregnated with Aluminium Oxide (A).

Application:

Fine fleece **for light cleaning work** and **a uniform surface finish**.

Note:

For matching the width of narrow rollers Ø 100×50 mm use the spacer ring pack No. 568439.

Technical description

recommended speed	2800 min ⁻¹
Grinding media backing	Cleaning non-woven abrasive mesh
Grit equivalent	180
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
Roller Ø	100 mm

Roller width	100 mm
Product name attribute	Ø 100 × 100 mm
Bore Ø	19 mm
Type of product	Abrasive flap wheel roller, fleece

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Paint	suitable only under restricted conditions		
dry	suitable		