



Bi-hexagon socket, 3/8 inch deep, Width across flats: 11 mm



Order data

Order number	637300 11
GTIN	4018754002177
Item class	63A

Description

Version:

Forged from high quality steel, internally bevelled for easy fitting to bolt heads. Internal square to **DIN 3120**.

Optimum grain orientation due to special forging process. Close tolerance sockets with **AS drive** profile protect corners of bolt head. Hardened in an oil bath, stress-relieved and distortion-free for a precision fit. Smoothed finish.

Standard:

DIN 3124-L

Material:

HPQ® high performance steel, non-flaking chrome-plated over nickel.

Technical description

Ø drive output end	15.6 mm
Length	54 mm
Width across flats	11 mm
Square drive	3/8 in
Drive profile	Bi-hex socket
Type of product	Socket insert

