



## Combination spanner set, Number of keys: 9



### Order data

Order number	613510 9
GTIN	4018754058273
Item class	63A

### Description

#### Version:

Drop-forged. With close tolerance jaw width.

With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission. Ring end with **AS-Drive** profile. (Sizes 3.2 – 5 with hexagon).

#### Standard:

**DIN 3113 A / ISO 3318 / ISO 7738**

#### Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

#### Supplied with:

1 each combination spanner No. 613600 / 613500 / 613800 / 613900 / 613950 / 613520 / 613970:  
Size 5.5; 7; 8; 10; 13; 16; 17; 18; 19

#### Note:

#### Advantage:

- **Bolts are gripped on the flanks. – The bolts are protected. – Longer bolt life.**
- **Larger contact surfaces between bolt and tool. – Secure grip and higher torque transmission.**

### Technical description

Number of keys	9
Width across flats	metric
Ring setting	15 degrees

Material	Chrome alloy steel
Surface	chrome-plated over nickel
Type of product	Spanner

---

## Accessories

Combination spanner Width across flats 10 mm	613500 10
Combination spanner Width across flats 13 mm	613500 13
Combination spanner Width across flats 16 mm	613500 16
Combination spanner Width across flats 19 mm	613500 19
Combination spanner Width across flats 5,5 mm	613500 5,5
Plastic clip holder with closure flap for number of sockets 11	611700 11
Plastic clip holder with closure flap for number of sockets 9	611700 9
Combination spanner Width across flats 7 mm	613500 7
Combination spanner Width across flats 8 mm	613500 8
Combination spanner Width across flats 17 mm	613500 17
Combination spanner Width across flats 18 mm	613500 18