




## Universal joint socket, 3/8 inch, Width across flats: 15mm



### Order data

Order number	637400 15
GTIN	4018754002511
Item class	63A

### Description

#### Version:

Forged from high quality steel, internally bevelled for easy fitting to bolt heads. Internal square to **DIN 3120**.

Optimum grain orientation due to special forging process. Close tolerance sockets with **AS drive** profile protect corners of bolt head. Hardened in an oil bath, stress-relieved and distortion-free for a precision fit. Smoothed finish.

#### Standard:

**DIN 3124 L**

#### Material:

HPQ® high performance steel, non-flaking chrome-plated over nickel.

### Technical description

Length	48.5 mm
∅ drive output end	20.6 mm
Width across flats	15 mm
Square drive	3/8 in
Drive profile	Bi-hex socket
Type of product	Socket insert

