




Universal joint socket, 3/8 inch, Width across flats: 17mm



Order data

Order number	637400 17
GTIN	4018754002535
Item class	63A

Description

Version:

Forged from high quality steel, internally bevelled for easy fitting to bolt heads. Internal square to **DIN 3120**.

Optimum grain orientation due to special forging process. Close tolerance sockets with **AS drive** profile protect corners of bolt head. Hardened in an oil bath, stress-relieved and distortion-free for a precision fit. Smoothed finish.

Standard:

DIN 3124 L

Material:

HPQ® high performance steel, non-flaking chrome-plated over nickel.

Technical description

Width across flats	17 mm
Length	53.5 mm
Ø drive output end	23 mm
Square drive	3/8 in
Drive profile	Bi-hex socket
Type of product	Socket insert

