

Bore Ø	22.23 mm
Disc Ø	150 mm
maximum speed	10200 min ⁻¹
Grinding media	Diamond
Grinding medium code	D
optimised for material	Stone
Shape	41
Shape description	straight
Propulsive equipment	Angle grinder
maximum circumferential speed	80 m/s
Type of product	Cutting disc