

LESSMANN®
THE GERMAN BRUSH COMPANY
**Wheel brush Steel wire 0.50 mm, Brush Ø D1× bore Ø d1 / thread M:
 115X22mm**

Order data

Order number	571200 115X22
GTIN	4017359005224
Item class	57L

Description
Version:

Straight round brush with smooth wire 0.50 mm, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.**

Application:

Left knotted, reliably avoids premature unwinding.

For heavy brush work, e.g. descaling, removing rust, removing paint, roughening, cleaning metal parts, also for cleaning formwork boards.

Technical description

Number of twisted knots	20
Length of brush section H ₁	24 mm
Brush Ø D ₁	115 mm
Bristle thickness	0.5 mm
maximum speed	12500 min ⁻¹

Bristle width L ₁	14 mm
Bore Ø d ₁	22 mm
Brush material	Steel wire
Twisted knotting	left-hand plait
Type of product	Wheel brush