

LESSMANN®
THE GERMAN BRUSH COMPANY

Dished bevel brush Stainless steel wire 0.50 mm, Brush Ø D1× thread M: 115XM14mm



Order data

Order number	571350 115XM14
GTIN	4017359044025
Item class	57L

Description

Version:

Dished **bevel brush** with smooth wire 0.50 mm, **knotted** and firmly crimped into the steel body.
Very aggressive brushing effect with high wear resistance.

Application:

Left knotted, reliably avoids premature unwinding.

Ideal for working where access is difficult and for heavy brush work, e.g. descaling, removing rust, removing paint, roughening, cleaning metal parts, also for cleaning formwork boards.

With **internal thread M14**, for direct mounting **on angle grinders**.

Technical description

Brush Ø D ₁	115 mm
Number of twisted knots	20
Length of brush section H ₁	24 mm
Bristle thickness	0.5 mm

maximum speed	12500 min ⁻¹
Bristle width L ₁	12 mm
Thread M	M14
Brush material	Stainless steel wire
Twisted knotting	left knotted
Type of product	Bevel brush