

LESSMANN®
THE GERMAN BRUSH COMPANY**Wheel brush Steel wire 0.50 mm, Brush Ø D1× bore Ø d1 / thread M:
178X22mm****Order data**

Order number	571200 178X22
GTIN	4017359005095
Item class	57L

Description**Version:**

Straight round brush with smooth wire 0.50 mm, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.**

Application:

Left knotted, reliably avoids premature unwinding.

For heavy brush work, e.g. descaling, removing rust, removing paint, roughening, cleaning metal parts, also for cleaning formwork boards.

Technical description

Bristle thickness	0.5 mm
maximum speed	12500 min ⁻¹
Brush Ø D ₁	178 mm
Length of brush section H ₁	38 mm
Number of twisted knots	32

Bristle width L_1	14 mm
Bore $\varnothing d_1$	22 mm
Brush material	Steel wire
Twisted knotting	left-hand plait
Type of product	Wheel brush