



Diamond cutting disc PREMIUM*** High-performance, Disc Ø: 125 mm



Order data

Order number	569740 125
GTIN	9003174645399
Item class	53T

Description

Version:

Diamond cutting discs for wet and dry cutting. Bore Ø 22.23 mm.

- **High cutting performance of diamonds gives short cutting times.**
- **Extremely long working life, fewer disc changes.**
- **Unvarying diameter, always cuts to the full depth.**
- **Hardly any disc wear, reducing dust generation.**

High-performance with 10 or 12 mm coating height. Suitable for all building materials, long working life, protected against overheating.

Application:

For cutting all common building materials such as concrete (even reinforced), bricks, natural stone, tiles, ceramics, steel etc.

Note:

- **Diamond coating already pre-sharpened. Observe correct direction of rotation!**
- **Other diamond cutting discs on request.**

maximum circumferential speed: 80 m/s

Bore Ø: 22.23 mm

Bore Ø: 22.23 mm

Technical description

Bore Ø	22.23 mm
Abrasive coating height	10 mm
Disc Ø	125 mm
maximum speed	12200 rpm
Grinding media	Diamond
Grinding medium code	D
Shape	41
Shape description	straight
maximum circumferential speed	80 m/s
Type of product	Cutting-off wheel