

LESSMANN®
THE GERMAN BRUSH COMPANY**Wheel brush Steel wire 0.50 mm, Brush Ø D1× bore Ø d1 / thread M:
200X22mm****Order data**

Order number	571200 200X22
GTIN	4017359013779
Item class	57L

Description**Version:**

Straight round brush with smooth wire 0.50 mm, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.**

Application:

Left knotted, reliably avoids premature unwinding.

For heavy brush work, e.g. descaling, removing rust, removing paint, roughening, cleaning metal parts, also for cleaning formwork boards.

Technical description

Brush Ø D ₁	200 mm
Bristle thickness	0.5 mm
maximum speed	9000 min ⁻¹
Length of brush section H ₁	41 mm
Number of twisted knots	36

Bristle width L ₁	14 mm
Bore Ø d ₁	22 mm
Brush material	Steel wire
Twisted knotting	left-hand plait
Type of product	Wheel brush