

LESSMANN®
THE GERMAN BRUSH COMPANY**Deburring wheel brush Steel wire 0.35 mm, Brush Ø D1× bristle width L1:
250X60mm****Order data**

Order number	570500 250X60
GTIN	4017359039052
Item class	57L

Description**Version:**

Bore diameter 50.8 mm with double keyway 13×7. Other bore diameters available.

Waved high-tensile **steel wire**.

Application:

For all popular bench deburring machines. Particularly long working life due to special wire. Ideally suited for economical deburring of flat strips, profiles, pipes, fittings, plastic parts, and the like.

Note:

Only the tips of the bristles act on the workpiece. Excessive applied pressure does not improve the result, but increases the required drive power and reduces the working life of the brush.

Technical description

Brush Ø D ₁	250 mm
Length of brush section H ₁	50 mm
maximum speed	3600 min ⁻¹

Brush width	58 mm
Brush material	Steel wire
Bristle thickness	0.35 mm
Propulsive equipment	Bench deburrer
Type of product	Wheel brush