

**TwinKey® multi-function key****Order data**

Order number	623550
GTIN	4003773074670
Item class	64D

Description**Version:**

2 four-way wrenches of die-cast zinc with reversible bit (Phillips and slot). The two wrenches are **linked with a magnet** to save space. When separated, two wrenches and the reversible bit are connected with a sturdy stainless steel cord so that they are captive.

Application:

Multi-function wrenches for operating locks in the field of building services (heating and sanitation, air conditioning and ventilation, electrical systems), gas and water supplies, and security systems.

Suitable for:

Square socket 5; 6–7; 8–9; 10–11 mm,
triangular socket 7–8; 9–10; 11–12 mm,
two-wing Ø 3–5 mm, half moon 6 mm,
stepped square plug 6; 7; 8; 9 mm, cross-head PH2,
slot-head 1.0×7 mm.

Technical description

overall length	95 mm
Manufacturer's designation	TwinKey

Drive profile	Square screwdriver
Drive profile	Triangular sockets
Drive profile	Square sockets
Drive profile	Hexagon sockets
Drive profile	Slot-head screwdriver
Drive profile	Screwdriver for Phillips
Drive profile	Half-moon
Drive profile	Two-wing key
Type of product	Control panel key