

LESSMANN®
THE GERMAN BRUSH COMPANY**Wheel brush Stainless steel wire 0.50 mm, Brush Ø D1× bore Ø d1 / thread M:
115X22mm****Order data**

Order number	571250 115X22
GTIN	4017359013687
Item class	57L

Description**Version:**

Straight round brush with smooth wire 0.50 mm, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.**

Application:

Left knotted, reliably avoids premature unwinding.

For heavy brush work, e.g. descaling, removing rust, removing paint, roughening, cleaning metal parts, also for cleaning formwork boards.

Technical description

Brush Ø D ₁	115 mm
Bristle thickness	0.5 mm
Length of brush section H ₁	24 mm
maximum speed	12500 min ⁻¹
Number of twisted knots	20

Bristle width L_1	14 mm
Bore $\varnothing d_1$	22 mm
Brush material	Stainless steel wire
Twisted knotting	left-hand plait
Type of product	Wheel brush