

LESSMANN®
THE GERMAN BRUSH COMPANY**Wheel brush Stainless steel wire 0.50 mm, Brush Ø D1× bore Ø d1 / thread M:
178X22mm****Order data**

Order number	571250 178X22
GTIN	4017359017753
Item class	57L

Description**Version:**

Straight round brush with smooth wire 0.50 mm, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.**

Application:

Left knotted, reliably avoids premature unwinding.

For heavy brush work, e.g. descaling, removing rust, removing paint, roughening, cleaning metal parts, also for cleaning formwork boards.

Technical description

Bristle thickness	0.5 mm
Length of brush section H ₁	38 mm
Brush Ø D ₁	178 mm
maximum speed	12500 min ⁻¹
Number of twisted knots	32

Bristle width L ₁	14 mm
Bore Ø d ₁	22 mm
Brush material	Stainless steel wire
Twisted knotting	left-hand plait
Type of product	Wheel brush