



Combination spanner, Width across flats: 10 mm



Order data

Order number	613700 10
GTIN	4045197159472
Item class	61A

Description

Version:

Drop-forged. With close tolerance jaw width.

With easy-grip profile shaft. Exceptional tool life and wear resistance. Ring end with **AS-Drive** profile.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

Note:

AS-Drive – the special profile. An extremely accurately fitting profile - developed for aviation and aerospace. Tools with this profile can be recognised by the **AS-Drive** symbol. **Advantages:**

- **Bolts are gripped on the flanks. – The bolts are protected. – Longer bolt life.**
- **Larger contact surfaces between bolt and tool. – Secure grip and higher torque transmission.**

Spanner length L: 125 mm

maximum jaw height h₁: 5 mm

maximum ring height h_{2 max}: 9 mm

Technical description

Spanner length L	125 mm
maximum jaw height h ₁	5 mm
Width across flats	10 mm
Width across flats	metric
maximum ring height h _{2 max}	9 mm

Ring setting

15 degrees