

LESSMANN®
THE GERMAN BRUSH COMPANY**Wheel brush Right-left knotted, stainless steel wire 0.50 mm, Brush Ø D1×
bore Ø d1 / thread M: 115X22mm****Order data**

Order number	571255 115X22
GTIN	4017359385845
Item class	57L

Description**Version:**

Straight round brush with smooth wire 0.50 mm, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.**

Application:

Right-left knotted for increased aggressiveness for heavy-duty brushing work. Very suitable for use at corners and edges, with a smooth action.

For heavy brush work, e.g. descaling, removing rust, removing paint, roughening, cleaning metal parts, also for cleaning formwork boards.

Technical description

Length of brush section H ₁	24 mm
Brush Ø D ₁	115 mm
Bristle thickness	0.5 mm
maximum speed	12500 min ⁻¹

Number of twisted knots	20
Bristle width L ₁	14 mm
Bore Ø d ₁	22 mm
Brush material	Stainless steel wire
Type of product	Wheel brush