



Combination spanner, phosphated, Width across flats: 25mm



Order data

Order number	613900 25
GTIN	4045197441577
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw width.
With oval shaft.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome vanadium steel, phosphated.

Technical description

maximum jaw height h1	12 mm
Spanner length L	290 mm
Width across flats	25 mm
Width across flats	metric
maximum ring height h_{2max}	16 mm
Ring setting	15 degrees
Material	Chrome vanadium steel
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner

