

LESSMANN®
THE GERMAN BRUSH COMPANY
Dished bevel brush Steel wire 0.50 mm, Brush Ø D1× thread M: 100XM14mm

Order data

| | |
|--------------|----------------|
| Order number | 571300 100XM14 |
| GTIN | 4017359041444 |
| Item class | 57L |

Description
Version:

Dished **bevel brush** with smooth wire 0.50 mm, **knotted** and firmly crimped into the steel body.

Very aggressive brushing effect with high wear resistance.

Application:

Left knotted, reliably avoids premature unwinding.

Ideal for working where access is difficult and for heavy brush work, e.g. descaling, removing rust, removing paint, roughening, cleaning metal parts, also for cleaning formwork boards.

With **internal thread M14**. for direct mounting **on angle grinders**.

Technical description

| | |
|--|-------------------------|
| Bristle thickness | 0.5 mm |
| Number of twisted knots | 18 |
| maximum speed | 12500 min ⁻¹ |
| Brush Ø D ₁ | 100 mm |
| Length of brush section H ₁ | 20 mm |

| | |
|------------------------------|--------------|
| Bristle width L ₁ | 12 mm |
| Thread M | M14 |
| Brush material | Steel wire |
| Twisted knotting | left knotted |
| Type of product | Bevel brush |