

**LESSMANN®**  
THE GERMAN BRUSH COMPANY
**Dished bevel brush Steel wire 0.50 mm, Brush Ø D1× thread M: 115XM14mm**

**Order data**

Order number	571300 115XM14
GTIN	4017359025772
Item class	57L

**Description**
**Version:**

Dished **bevel brush** with smooth wire 0.50 mm, **knotted** and firmly crimped into the steel body.  
**Very aggressive brushing effect with high wear resistance.**

**Application:**

**Left knotted**, reliably avoids premature unwinding.

Ideal for working where access is difficult and for heavy brush work, e.g. descaling, removing rust, removing paint, roughening, cleaning metal parts, also for cleaning formwork boards.

With **internal thread M14**. for direct mounting **on angle grinders**.

**Technical description**

Number of twisted knots	20
Brush Ø D <sub>1</sub>	115 mm
Length of brush section H <sub>1</sub>	24 mm
maximum speed	12500 min <sup>-1</sup>
Bristle thickness	0.5 mm

Bristle width L <sub>1</sub>	12 mm
Thread M	M14
Brush material	Steel wire
Twisted knotting	left knotted
Type of product	Bevel brush