



Combination spanner, phosphated, Width across flats: 7mm



Order data

Order number	613900 7
GTIN	4045197385109
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw width.
With oval shaft.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome vanadium steel, phosphated.

Technical description

Spanner length L	110 mm
maximum jaw height h1	4 mm
Width across flats	7 mm
Width across flats	metric
maximum ring height h_{2max}	7 mm
Ring setting	15 degrees
Material	Chrome vanadium steel
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner

