



Combination spanner, Width across flats: 27 mm



Order data

Order number	613700 27
GTIN	4045197159618
Item class	61A

Description

Version:

Drop forged. With close tolerance jaw width.

With easy-grip profile shaft. Exceptional tool life and wear resistance. Ring end with **AS-drive** profile.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

Note:

AS drive – the special profile. An extremely accurately fitting profile - developed for aviation and aerospace. Tools with this profile can be recognised by the **AS-drive** symbol. **Advantages:**

- **Bolts are gripped on the flanks. – The bolts are protected. – Longer bolt life.**
- **Larger contact surfaces between bolt and tool. – Secure grip and higher torque transmission.**

Spanner length L: 300 mm

maximum jaw height h₁: 13 mm

maximum ring height h_{2 max}: 18 mm

Technical description

Width across flats	27 mm
maximum jaw height h ₁	13 mm
Spanner length L	300 mm
Width across flats	metric
maximum ring height h _{2 max}	18 mm

Ring setting

15 degrees