



## Combination spanner, Width across flats: 15 mm



### Order data

Order number	613700 15
GTIN	4045197159526
Item class	61A

### Description

#### Version:

Drop forged. With close tolerance jaw width.

With easy-grip profile shaft. Exceptional tool life and wear resistance. Ring end with **AS-drive** profile.

#### Standard:

**DIN 3113 A / ISO 3318 / ISO 7738**

#### Material:

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

#### Note:

**AS drive** – the special profile. An extremely accurately fitting profile - developed for aviation and aerospace. Tools with this profile can be recognised by the **AS-drive** symbol. **Advantages:**

- **Bolts are gripped on the flanks. – The bolts are protected. – Longer bolt life.**
- **Larger contact surfaces between bolt and tool. – Secure grip and higher torque transmission.**

Spanner length L: 170 mm

maximum jaw height h1: 7 mm

maximum ring height  $h_{2\max}$ : 12 mm

### Technical description

Spanner length L	170 mm
maximum jaw height h1	7 mm
Width across flats	15 mm
Width across flats	metric
maximum ring height $h_{2\max}$	12 mm

Ring setting

15 degrees