



Combination spanner set, phosphated, Number of keys: 23



Order data

Order number	613910 23
GTIN	4045197385321
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw width.

With oval shaft.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome vanadium steel, phosphated.

Supplied with:

1 each combination spanner No. 613600 / 613500 / 613800 / 613900 / 613950 / 613520 / 613970:

Size 5.5; 6; 7; 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 20; 21; 22; 24; 27; 30; 32; 34

Technical description

Number of keys	23
Width across flats	metric
Ring setting	15 degrees
Material	Chrome vanadium steel
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner

Accessories

Combination spanner Width across flats 9 mm	613900 9
Combination spanner Width across flats 6 mm	613900 6
Combination spanner Width across flats 8 mm	613900 8
Combination spanner Width across flats 17 mm	613900 17
Combination spanner Width across flats 10 mm	613900 10
Combination spanner Width across flats 5,5 mm	613900 5,5
Combination spanner Width across flats 27 mm	613900 27
Combination spanner Width across flats 15 mm	613900 15
Combination spanner Width across flats 16 mm	613900 16
Combination spanner Width across flats 14 mm	613900 14
Combination spanner Width across flats 12 mm	613900 12
Combination spanner Width across flats 18 mm	613900 18
Combination spanner Width across flats 22 mm	613900 22
Combination spanner Width across flats 19 mm	613900 19
Combination spanner Width across flats 20 mm	613900 20
Combination spanner Width across flats 32 mm	613900 32
Combination spanner Width across flats 30 mm	613900 30
Combination spanner Width across flats 11 mm	613900 11
Combination spanner Width across flats 34 mm	613900 34
Combination spanner Width across flats 13 mm	613900 13
Combination spanner Width across flats 24 mm	613900 24
Combination spanner Width across flats 21 mm	613900 21
Combination spanner Width across flats 7 mm	613900 7