



## Combination spanner, Width across flats: 5,5 mm



### Order data

Order number	613700 5,5
GTIN	4045197159427
Item class	61A

### Description

#### Version:

Drop forged. With close tolerance jaw width.

With easy-grip profile shaft. Exceptional tool life and wear resistance. Ring end with **AS-drive** profile.

#### Standard:

**DIN 3113 A / ISO 3318 / ISO 7738**

#### Material:

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

#### Note:

**AS drive** – the special profile. An extremely accurately fitting profile - developed for aviation and aerospace. Tools with this profile can be recognised by the **AS-drive** symbol. **Advantages:**

- **Bolts are gripped on the flanks. – The bolts are protected. – Longer bolt life.**
- **Larger contact surfaces between bolt and tool. – Secure grip and higher torque transmission.**

Spanner length L: 100 mm

maximum jaw height h1: 4 mm

maximum ring height h<sub>2max</sub>: 6 mm

### Technical description

Spanner length L	100 mm
maximum jaw height h1	4 mm
Width across flats	5.5 mm
Width across flats	metric
maximum ring height h <sub>2max</sub>	6 mm

Ring setting

15 degrees