

**Combination spanner, phosphated, Width across flats: 9mm****Order data**

Order number	613900 9
GTIN	4045197385116
Item class	62A

Description**Version:**

Drop-forged. With close tolerance jaw width.
With oval shaft.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome vanadium steel, phosphated.

Technical description

Spanner length L	130 mm
maximum jaw height h1	4.5 mm
Width across flats	9 mm
Width across flats	metric
maximum ring height $h_{2\max}$	8 mm
Ring setting	15 degrees
Material	Chrome vanadium steel
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner

