

**Combination spanner, phosphated, Width across flats: 34mm****Order data**

Order number	613900 34
GTIN	4045197385260
Item class	62A

Description**Version:**

Drop-forged. With close tolerance jaw width.
With oval shaft.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome vanadium steel, phosphated.

Technical description

Width across flats	34 mm
maximum jaw height h1	14 mm
Spanner length L	380 mm
Width across flats	metric
maximum ring height h_{2max}	21 mm
Ring setting	15 degrees
Material	Chrome vanadium steel
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner

