



Combination spanner, phosphated, Width across flats: 10mm



Order data

| | |
|--------------|---------------|
| Order number | 613900 10 |
| GTIN | 4045197348661 |
| Item class | 62A |

Description

Version:

Drop-forged. With close tolerance jaw width.
With oval shaft.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome vanadium steel, phosphated.

Technical description

| | |
|---------------------------------|-----------------------|
| maximum jaw height h1 | 5 mm |
| Spanner length L | 140 mm |
| Width across flats | 10 mm |
| Width across flats | metric |
| maximum ring height $h_{2\max}$ | 9 mm |
| Ring setting | 15 degrees |
| Material | Chrome vanadium steel |
| Surface | phosphated |
| Product name attribute | phosphated |
| Type of product | Spanner |

