

**Combination spanner, phosphated, Width across flats: 36mm****Order data**

Order number	613900 36
GTIN	4045197385277
Item class	62A

**Description****Version:**

Drop-forged. With close tolerance jaw width.  
With oval shaft.

**Standard:**

**DIN 3113 A / ISO 3318 / ISO 7738**

**Material:**

Chrome vanadium steel, phosphated.

**Technical description**

Spanner length L	400 mm
maximum jaw height h1	15 mm
Width across flats	36 mm
Width across flats	metric
maximum ring height $h_{2max}$	24 mm
Ring setting	15 degrees
Material	Chrome vanadium steel
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner

