



Combination spanner, chrome-plated, Width across flats: 4,5mm



Order data

Order number	613950 4,5
GTIN	4045197441614
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw width.
With oval shaft.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome vanadium steel, chrome-plated.

Technical description

Spanner length L	100 mm
Width across flats	4.5 mm
maximum jaw height h ₁	4 mm
Width across flats	metric
maximum ring height h _{2 max}	6 mm
Standard	DIN 3113 A
Standard	ISO 3318
Standard	ISO 7738
Ring setting	15 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel

Surface	chrome plated
Product name attribute	chrome-plated
Type of product	Spanner