



## Combination spanner, phosphated, Width across flats: 11 mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 613900 11     |
| GTIN         | 4045197385123 |
| Item class   | 62A           |

### Description

**Version:**

Drop-forged. With close tolerance jaw width.  
With oval shaft.

**Standard:**

**DIN 3113 A / ISO 3318 / ISO 7738**

**Material:**

Chrome vanadium steel, phosphated.

### Technical description

|                                 |                       |
|---------------------------------|-----------------------|
| Spanner length L                | 150 mm                |
| Width across flats              | 11 mm                 |
| maximum jaw height h1           | 5.5 mm                |
| Width across flats              | metric                |
| maximum ring height $h_{2\max}$ | 10 mm                 |
| Ring setting                    | 15 degrees            |
| Material                        | Chrome vanadium steel |
| Surface                         | phosphated            |
| Product name attribute          | phosphated            |
| Type of product                 | Spanner               |

