



Combination spanner set, Number of keys: 23



Order data

Order number	613710 23
GTIN	4045197159700
Item class	61A

Description

Version:

Drop forged. With close tolerance jaw width.

With easy-grip profile shaft. Exceptional tool life and wear resistance. Ring end with **AS-drive** profile.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

Supplied with:

1 each spanner No. 613700 / 613500 / 613900 / 613950 / 613520 / 613970: Size 5.5; 6; 7; 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 20; 21; 22; 24; 27; 30; 32; 34

Note:

AS drive – the special profile. An extremely accurately fitting profile - developed for aviation and aerospace. Tools with this profile can be recognised by the **AS drive** symbol. **Advantages:**

- **Bolts are gripped on the flanks. – The bolts are protected. – Longer working life of the bolt.**
- **Larger contact surfaces between bolt and tool. – Secure grip and higher torque transmission.**

Technical description

Number of keys	23
----------------	----

Width across flats	metric
Ring setting	15 degrees
Material	Chrome alloy steel
Surface	chrome-plated over nickel