

**Combination spanner, phosphated, Width across flats: 22mm****Order data**

Order number	613900 22
GTIN	4045197385215
Item class	62A

**Description****Version:**

Drop-forged. With close tolerance jaw width.  
With oval shaft.

**Standard:**

**DIN 3113 A / ISO 3318 / ISO 7738**

**Material:**

Chrome vanadium steel, phosphated.

**Technical description**

Spanner length L	260 mm
maximum jaw height h1	10 mm
Width across flats	22 mm
Width across flats	metric
maximum ring height $h_{2max}$	15 mm
Ring setting	15 degrees
Material	Chrome vanadium steel
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner

