



## Combination spanner, phosphated, Width across flats: 4mm



### Order data

Order number	613900 4
GTIN	4045197441539
Item class	62A

### Description

**Version:**

Drop-forged. With close tolerance jaw width.  
With oval shaft.

**Standard:**

**DIN 3113 A / ISO 3318 / ISO 7738**

**Material:**

Chrome vanadium steel, phosphated.

### Technical description

maximum jaw height h1	4 mm
Width across flats	4 mm
Spanner length L	100 mm
Width across flats	metric
maximum ring height $h_{2max}$	6 mm
Ring setting	15 degrees
Material	Chrome vanadium steel
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner

