

**Combination spanner set, phosphated, Number of keys: 9****Order data**

Order number	613910 9
GTIN	4045197385284
Item class	62A

Description**Version:**

Drop-forged. With close tolerance jaw width.
With oval shaft.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome vanadium steel, phosphated.

Supplied with:

1 each combination spanner No. 613600 / 613500 / 613800 / 613900 / 613950 / 613520 / 613970:
Size 5.5; 7; 8; 10; 13; 16; 17; 18; 19

Technical description

Number of keys	9
Width across flats	metric
Ring setting	15 degrees
Material	Chrome vanadium steel
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner

Accessories

Plastic clip holder with closure flap for number of sockets 11	611700 11
Plastic clip holder with closure flap for number of sockets 9	611700 9
Combination spanner Width across flats 17 mm	613900 17
Combination spanner Width across flats 13 mm	613900 13
Combination spanner Width across flats 8 mm	613900 8
Combination spanner Width across flats 5,5 mm	613900 5,5
Combination spanner Width across flats 18 mm	613900 18
Combination spanner Width across flats 16 mm	613900 16
Combination spanner Width across flats 10 mm	613900 10
Combination spanner Width across flats 7 mm	613900 7
Combination spanner Width across flats 19 mm	613900 19